

ITCOGEL T 250

ITCOGEL T 250 Tube Filling Compound (Thixotropic Jelly) is a soft, non-melting, transparent, water barrier compound. It is based on synthetic and aliphatic hydrocarbons and has been formulated to meet a wide range of processing and performance requirements. It is used in filling, buffering of loose tube and direct laid fibres in slotted core and ribbon designs of Optical Fibre Cables.

ITCOGEL T 250 exhibits good stability over a wide temperature range of - 40°C to + 85°C.

Appearance	Transparent Gel without visible impurities	Visual (Erichsen Gauge 100 μ)
Flash Point COC - °C	> 230	ASTM D 92
Drop Point - °C	> 200	ASTM D 566
Viscosity at 25°C, 100 rpm - cps Typical Values : 10 rpm 100 rpm	9500 ± 1000 38400 9600	Brookfield Viscometer HADV, Spindle No. 7
Viscosity (Typical) at 25°C, D = 50 1/S - mPas	4500	Haake Rheometer RV1 (DIN 53019)
Cone Penetration - 1/10 mm at + 25°C at - 40°C at - 30°C Typical Values : + 25°C - 30°C - 40°C	≥ 390 > 200 > 250 410 285 225	ASTM D 937
Density at 25°C - g/cm ³	0.83 ± 0.01	ASTM D 1217
Volatility, 24 hrs at 150°C - %	< 1	FTM 791 C
Oil Separation, 24 hrs at 150°C - %	Zero	FTM 791 C
Oxidation Induction Time, 190°C, Alu. Pan – minutes	> 30	ASTM D 3895
Tube Drainage in 2.00 mm ID Empty Tube, 24 hrs at 80°C	Pass	ITCO : ITM 09
Hydrogen Generation, 24 hrs at 80°C - μl/g	< 0.03	ITCO : ITM 28
Glass Transition Temperature (Typical)	≤ - 60°C	ASTM D 3418

Packing In metal drums with epoxy lining : Height – 885 mm, Internal Diameter – 570 mm, 170 Kg Nett weight. Bulk Bag (Fluid Bag) with 700 / 750 Kg Nett weight.

Storage Minimum 3 years in original packed condition stored at room temperature.

Safety As per our knowledge and available information, ITCOGEL T 250 does not pose any health hazard. For further information, please refer to MSDS a copy of which is available upon request.

Compatibility ITCOGEL T series products have been tested and found compatible with most of the associated cable materials including Fibre Coatings and Colouring Inks. Further information is available upon request.